



Cellular Minimum Mounting Depth Requirement

Product ID: 503415, 503414

Semi Inside Mount  Partially Protruding Out of the Window Opening	Lift Type	Lift Control Type	3/8" Single	9/16" Single	3/4" Single or 1/2" Double	3/4" Double or 1 1/4" Single
	Corded	Bottom Up/ Top Down Bottom Up/ Day&Night	1-1/8"	1-3/8"	1-3/8"	1-5/8"
	Cordloop	Bottom Up/ SmartRelease™/ Top Down	1-1/4"	1-1/4"	1-1/4"	1-1/2"
	Cordless	Bottom Up/ Top Down Bottom Up/ Day&Night	1-1/4"	1-1/4"	1-1/4"	1-1/2"
	Cordless (Woven Colors) Available in Single Cell only	Bottom Up/ Top Down Bottom Up	N/A	N/A	1-3/8"	1-1/2"
	Motorization	Bottom Up/ Top Down Bottom Up / Day&Night	1-1/4"	1-1/4"	1-1/4"	1-3/4"

Inside Mount  Flush with the Window Opening	Lift Type	Lift Control Type	3/8" Single	9/16" Single	3/4" Single or 1/2" Double	3/4" Double or 1 1/4" Single
	Corded	Bottom Up/ Top Down Bottom Up/ Day&Night	1-3/8"	1-3/4"	2-1/8"	2-3/4"
	Cordloop	Bottom Up/ SmartRelease™/ Top Down	2-3/8"	2-3/8"	2-3/8"	2-3/4"
	Cordless	Bottom Up	1-7/8"	1-7/8"	2"	2-3/4"
		Top Down Bottom Up/ Day&Night	2"	2"	2"	2-3/4"
	Cordless (Woven Colors) Available in Single Cell only	Bottom Up/ Top Down Bottom Up	N/A	N/A	2-1/8"	2-3/4"
	Motorization	Bottom Up/ Top Down Bottom Up / Day&Night	2-3/8"	2-3/8"	2-3/8"	2-7/8"
	ClearFit™	Top Down Bottom Up	1-3/8" *	1-7/8"	1-7/8"	2-3/4"

* ClearFit™ without light guard will only need 1 1/4" for 3/8" single cell size.

The above measurements are rounded to provide a simplified version. Please refer to the spec book for the exact minimum depths.